



PRODUCT-DETAILS

3GAA092062-ASA

No Description Available

"No longer for sale" replaced by 3GAA092002-

General Information	
Product ID	3GAA092062-ASA
ABB Type Designation	M1AA 90LA 4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M1AA 90LA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6305-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Türkiye (TR)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	1.50 kW	1420 r/min	6.20 A	0.780
Y	--	50 Hz	400 V	1.50 kW	1420 r/min	3.60 A	0.780
Y	--	60 Hz	460 V	1.50 kW	1725 r/min	3.10 A	0.740

Frame Material	Aluminum
Frame Size	90
Gross Weight	0 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 77.2 % Partial Load (75%) 76.5 % Partial Load (50%) 73.9 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton

Product Name	3-Phase squirrel cage motor
Product Net Weight	0 kg
Product Type	1AA1__M1AA_IE1_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA092002-ASE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)