



PRODUCT-DETAILS

3GAA092312-BDE

No Description Available

"No longer for sale" replaced by 3GAA092314-

General Information								
Product ID				3GAA092312-BDE				
ABB Type Designation				M3AA 90L 4				
Catalog Description				No Description Available				
Additional Information								
ABB Type Designation				M3AA 90L 4				
Altitude				1000 m				
Ambient Temperature				40 °C				
Bearing				6205-2Z/C3				
Bearing NDE				6204-2Z/C3				
Core Credit				0.00				
Country of Origin				Spain (ES) Sweden (SE)				
Customs Tariff Number				85015220				
Direction of Rotation				Both sides				
Electrical Data								
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque
Y	--	50 Hz	660-690 V	1.10 kW	1420 r/min	1.50 A	0.800	7.40 N·m
D	--	50 Hz	380-420 V	1.10 kW	1420 r/min	2.50 A	0.800	7.40 N·m
D	--	60 Hz	440-480 V	1.30 kW	1720 r/min	2.50 A	0.800	7.22 N·m
Frame Size				90				
Gross Weight				16.48 kg				
IC Class				IC411				
IM Class				IMB5 IM3001				
Insulation Class				ICLF				
IP Class				IP55				
Lubrication				For life				
Made To Order				No				
Minimum Order Quantity				1 piece				
Number of Poles (High)				4				
Package Level 1 Units				0 carton				
Product Name				3-Phase squirrel cage motor				

Product Net Weight	16 kg
Product Type	3AA1__M3AA_IE1_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA092312-BDC
Replacement Product ID (NEW)	3GAA092314-BDE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)