



PRODUCT-DETAILS

3GAA093002-BSESK2

No Description Available

"No longer for sale" replaced by 3GAA093002-

General Information	
Product ID	3GAA093002-BSESK2
ABB Type Designation	M2AA 090 L-6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2AA 090 L-6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	Romania (RO)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	tE
Y	--	50 Hz	380 V	1.10 kW	890 r/min	3.30 A	0.690	72.90 %	0.00 N·m	0.00	
Y	--	50 Hz	400 V	1.10 kW	915 r/min	3.40 A	0.630	0.00 %	0.00 N·m	0.00	
Y	--	50 Hz	415 V	1.10 kW	920 r/min	3.50 A	0.590	0.00 %	0.00 N·m	0.00	
Y	--	60 Hz	380 V	1.10 kW	1075 r/min	3.10 A	0.730	0.00 %	0.00 N·m	0.00	0
D	--	60 Hz	220 V	1.10 kW	1075 r/min	5.40 A	0.730	0.00 %	0.00 N·m	0.00	0
Y	--	60 Hz	460 V	1.10 kW	1125 r/min	3.10 A	0.590	0.00 %	0.00 N·m	0.00	0

Frame Size	90
Gross Weight	16.48 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55W
Lubrication	For life

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	16 kg
Product Type	2AA2__M2AA__IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA093002-BSA
Replacement Product ID (NEW)	3GAA093002-BSESK3
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S