


PRODUCT-DETAILS

3GAA093520-BRE  
(3GAA093520-BRE)



General Information	
Product ID	3GAA093520-BRE
ABB Type Designation	M3AA 90LB 6
Catalog Description	(3GAA093520-BRE)

Ordering	
ABB Type Designation	M3AA 90LB 6
Invoice Description	M3AA 90LB 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	60 Hz	380 V	0.75 kW	1150 r/min	2.20 A	0.630
D	--	60 Hz	220 V	0.75 kW	1150 r/min	3.80 A	0.630

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	R

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	18 kg
Gross Weight	21 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

