


PRODUCT-DETAILS

3GAA108524-ADF

(3GAA108524-ADF)



General Information	
Product ID	3GAA108524-ADF
ABB Type Designation	M3AA 100LB 4/6
Catalog Description	(3GAA108524-ADF)

Ordering	
ABB Type Designation	M3AA 100LB 4/6
Invoice Description	M3AA 100LB 4/6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA108204-ADE

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.50 kW	1430 r/min	5.50 A	0.840	79.00 %	16.00 N·m	5.60
Y	--	50 Hz	400 V	0.80 kW	960 r/min	2.50 A	0.710	68.00 %	7.90 N·m	3.50
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 68.0 % Partial Load (75%) 65.0 % Partial Load (50%) 55.7 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	23 kg
Gross Weight	28 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

