

PRODUCT-DETAILS

3GAA131001-ADB

No Description Available

"No longer for sale" replaced by 3GAA131001-



General Information

Product ID	3GAA131001-ADB
ABB Type Designation	M2AA 132SA 2
Catalog Description	No Description Available

Ordering

ABB Type Designation	M2AA 132SA 2
Product Name	3-Phase squirrel cage motor
Product Type	2AA1__M2AA_IE1_AA
Made To Order	No
Minimum Order Quantity	1 piece
Selling Unit of Measure	piece
Country of Origin	Spain (ES)
Customs Tariff Number	85015220

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	tE
Y	--	50 Hz	660-690 V	5.50 kW	2855 r/min	6.30 A	0.880	0.00 %	18.40 N·m	0.00	
D	--	50 Hz	380-420 V	5.50 kW	2855 r/min	10.90 A	0.880	0.00 %	18.40 N·m	0.00	0
D	--	60 Hz	440-480 V	6.40 kW	3455 r/min	10.90 A	0.880	0.00 %	17.69 N·m	0.00	0

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical	
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	1 carton
Product Net Weight	37 kg
Gross Weight	38.38 kg

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories	
------------	--

Motors and Generators → IEC Low Voltage AC Motors → Brake Motors

Motors and Generators → IEC Low Voltage AC Motors → Legacy IEC Low Voltage Motors → Aluminum Motors

Motors and Generators → IEC Low Voltage AC Motors → Marine Motors → Marine General Performance Motors

