



PRODUCT-DETAILS

3GAA131313-JDE

M3AA 132SC 2

"No longer for sale" replaced by 3GAA131130-

General Information											
Product ID	3GAA131313-JDE										
ABB Type Designation	M3AA 132SC 2										
Catalog Description	M3AA 132SC 2										
Additional Information											
ABB Type Designation	M3AA 132SC 2										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6208-2Z/C3										
Bearing NDE	6206-2Z/C3										
Country of Origin	Spain (ES) Sweden (SE) Poland (PL)										
Customs Tariff Number	85015220										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	690 V	7.50 kW	2915 r/min	8.00 A	0.870	88.50 %	24.50 N-m	7.60
	D	--	50 Hz	400 V	7.50 kW	2915 r/min	14.00 A	0.870	88.50 %	24.50 N-m	7.60
	D	--	60 Hz	460 V	7.50 kW	3520 r/min	11.80 A	0.890	89.50 %	20.30 N-m	8.70
Frame Size	132										
Gross Weight	57.38 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 88.5 % Partial Load (75%) 88.7 % Partial Load (50%) 88.1 %										
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 89.5 %										
IM Class	IMB34 IM2101										
Insulation Class	ICLF										

Invoice Description	M3AA 132SC 2
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	56 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA131024-JDC 3GAA131213-JDE
Replacement Product ID (NEW)	3GAA131130-JDE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D