



## PRODUCT-DETAILS

# 3GAA131443-ADE

## No Description Available

## "No longer for sale" replaced by 3GAA131130-

### General Information

Product ID	3GAA131443-ADE
ABB Type Designation	M3AA 132SC 2
EAN	3GAA131443-ADE
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M3AA 132SC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
EAN	3GAA131443-ADE

#### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	tE
Y	--	50 Hz	660-690 V	7.50 kW	2905 r/min	8.30 A	0.920	0.00 %	24.66 N·m	0.00	
D	--	50 Hz	380-420 V	7.50 kW	2905 r/min	14.40 A	0.920	0.00 %	24.66 N·m	0.00	0
D	--	60 Hz	440-480 V	8.60 kW	3475 r/min	14.40 A	0.900	0.00 %	23.63 N·m	0.00	0

Frame Material	Aluminum
Frame Size	132
Gross Weight	56 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece

Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	56 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA131130-ADE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D