



PRODUCT-DETAILS

3GAA131443-AHE

No Description Available

"No longer for sale" replaced by 3GAA131130-

General Information

Product ID	3GAA131443-AHE
ABB Type Designation	M3AA 132SC 2
EAN	3GAA131443-AHE
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 132SC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Spain (ES) China (CN) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GAA131443-AHE

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	7.50 kW	2920 r/min	13.20 A	0.890

Frame Size	132
Gross Weight	56 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 88.2 % Partial Load (75%) 88.4 % Partial Load (50%) 86.9 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor

Product Net Weight	56 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA131130-AHE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H