



PRODUCT-DETAILS

3GAA132313-BRE

No Description Available

"No longer for sale" replaced by 3GAA132320-

General Information

Product ID	3GAA132313-BRE
ABB Type Designation	M3AA 132MB 4
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 132MB 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency
D	--	60 Hz	220 V	11.00 kW	1760 r/min	41.20 A	0.770	91.00 %
Y	--	60 Hz	380 V	11.00 kW	1760 r/min	23.80 A	0.770	91.00 %

Frame Size	132
Gross Weight	60.38 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	59 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA132320-BRE

Selling Unit of Measure	piece
Standards	IEC 60034-1
Stocked At (Warehouses)	Menden, Germany
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	R