



## PRODUCT-DETAILS

# 3GAA132444-BHE

## No Description Available

## "No longer for sale" replaced by 3GAA132310-

### General Information

Product ID	3GAA132444-BHE
ABB Type Designation	M3AA 132MA 4
EAN	3GAA132444-BHE
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M3AA 132MA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Spain (ES) China (CN) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GAA132444-BHE

### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	7.50 kW	1460 r/min	14.50 A	0.810

Frame Size	132
Gross Weight	59 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 88.7 % Partial Load (75%) 89.1 % Partial Load (50%) 88.0 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor

Product Net Weight	59 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA132310-BHE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H