



PRODUCT-DETAILS

3GAA132614-BDJ

No Description Available

"No longer for sale" replaced by 3GAA132310-

General Information								
Product ID	3GAA132614-BDJ							
ABB Type Designation	M3AA 132MA 4							
Catalog Description	No Description Available							
Additional Information								
ABB Type Designation	M3AA 132MA 4							
Altitude	1000 m							
Ambient Temperature	40 °C							
Bearing	6208-2Z/C3							
Bearing NDE	6206-2Z/C3							
Country of Origin	Poland (PL) Sweden (SE)							
Customs Tariff Number	85015220							
Direction of Rotation	Both sides							
Electrical Data								
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
	D	--	50 Hz	400 V	7.50 kW	1462 r/min	15.00 A	0.790
	Y	--	50 Hz	690 V	7.50 kW	1461 r/min	8.00 A	0.800
	D	--	50 Hz	415 V	7.50 kW	1465 r/min	15.10 A	0.760
Frame Material	Aluminum							
Frame Size	132							
Gross Weight	60 kg							
IC Class	IC411							
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 90.6 % Partial Load (75%) 91.3 % Partial Load (50%) 90.6 %							
IM Class	IMB5 IM3001							
Insulation Class	ICLF							
IP Class	IP55							
Made To Order	No							
Minimum Order Quantity	1 piece							
Number of Poles (High)	4							
Order Multiple	1 piece							

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	59 kg
Product Type	3AA0__M3AA_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA132310-BDJ
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Temperature Rise	80 K
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D