



PRODUCT-DETAILS

3GAA133212-ADE

No Description Available

General Information	
Product ID	3GAA133212-ADE
ABB Type Designation	M2AA 132MA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2AA 132MA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Spain (ES)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	690 V	4.00 kW	960 r/min	5.70 A	0.680
D	--	50 Hz	400 V	4.00 kW	960 r/min	10.00 A	0.680
D	--	60 Hz	460 V	4.00 kW	1165 r/min	8.70 A	0.670

Frame Size	132
Gross Weight	47.380 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
	Full Load (100%) 84.9 %
	Partial Load (75%) 85.3 %
IE Class Data (60 Hz)	Partial Load (50%) 83.9 %
	IE Class IE1
	Full Load (100%) 85.4 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP 55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1.000 piece
Number of Poles (High)	6

Order Multiple	1.000 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	46.000 kg
Quote Only	No
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Selling Unit of Measure	piece
Standards	IEC 60034-1
Stocked At (Warehouses)	Västerås, Sweden
Temperature Class Default	--
Temperature Rise Class	TCLB
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)