



PRODUCT-DETAILS

3GAA133310-HDE

No Description Available

"No longer for sale" replaced by 3GAA133320-

| General Information | | | | | | | | | | | |
|------------------------|----------------------------|------------|-------|---------|---------|------------|---------|--------------|------------|-----------|---|
| Product ID | 3GAA133310-HDE | | | | | | | | | | |
| ABB Type Designation | M3AA 132MA 6 | | | | | | | | | | |
| Catalog Description | No Description Available | | | | | | | | | | |
| Additional Information | | | | | | | | | | | |
| ABB Type Designation | M3AA 132MA 6 | | | | | | | | | | |
| Bearing | 6208-2Z/C3 | | | | | | | | | | |
| Bearing NDE | 6206-2Z/C3 | | | | | | | | | | |
| Country of Origin | Finland (FI) China (CN) | | | | | | | | | | |
| Customs Tariff Number | 85015220 | | | | | | | | | | |
| Direction of Rotation | Both sides | | | | | | | | | | |
| Electrical Data | | | | | | | | | | | |
| | Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
| | Y | -- | 50 Hz | 690 V | 4.00 kW | 960 r/min | 5.80 A | 0.680 | 84.90 % | 39.70 N·m | 4.60 |
| | D | -- | 50 Hz | 400 V | 4.00 kW | 960 r/min | 10.00 A | 0.680 | 84.90 % | 39.70 N·m | 4.60 |
| | D | -- | 60 Hz | 460 V | 4.00 kW | 1160 r/min | 8.75 A | 0.670 | 85.60 % | 32.90 N·m | 5.10 |
| Frame Material | | | | | | | | | | | Aluminum |
| Frame Size | | | | | | | | | | | 132 |
| Gross Weight | | | | | | | | | | | 51 kg |
| IC Class | | | | | | | | | | | IC411 |
| IE Class Data (50 Hz) | | | | | | | | | | | IE Class IE2 Full Load (100%) 84.9 % Partial Load (75%) 85.3 % Partial Load (50%) 83.9 % |
| IE Class Data (60 Hz) | | | | | | | | | | | IE Class IE1 Full Load (100%) 85.4 % Partial Load (75%) 85.6 % Partial Load (50%) 83.6 % |
| IM Class | | | | | | | | | | | IMB35 IM2001 |
| Insulation Class | | | | | | | | | | | ICLF |
| IP Class | | | | | | | | | | | IP55 |
| Made To Order | | | | | | | | | | | No |

| | |
|-------------------------------|-----------------------------|
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 6 |
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 carton |
| Pre Modified Motor Product ID | 3GAA133310-ADE |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 46 kg |
| Product Type | 3AA2__M3AA_IE2_AA |
| Quote Only | No |
| Replacement Product ID (NEW) | 3GAA133320-HDE |
| Selling Unit of Measure | piece |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| UNSPSC | 26101100 |
| Voltage Code | D |