



PRODUCT-DETAILS

3GAA133310-HSE

No Description Available

"No longer for sale" replaced by 3GAA133320-

General Information	
Product ID	3GAA133310-HSE
ABB Type Designation	M3AA 132MA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 132MA 6
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Finland (FI) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	4.00 kW	960 r/min	10.00 A	0.680	84.90 %	39.70 N-m	4.60
D	--	50 Hz	230 V	4.00 kW	960 r/min	17.60 A	0.680	84.90 %	39.80 N-m	4.60
Y	--	50 Hz	415 V	4.00 kW	965 r/min	9.60 A	0.670	86.00 %	39.70 N-m	4.80
Y	--	60 Hz	460 V	4.00 kW	1160 r/min	8.75 A	0.670	85.60 %	32.90 N-m	5.10

Frame Material	Aluminum
Frame Size	132
Gross Weight	51 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 84.9 % Partial Load (75%) 85.3 % Partial Load (50%) 83.9 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 85.4 % Partial Load (75%) 85.6 % Partial Load (50%) 83.6 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Pre Modified Motor Product ID	3GAA133310-ASE
Product Name	3-Phase squirrel cage motor
Product Net Weight	46 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA133320-HSE
Selling Unit of Measure	piece
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
UNSPSC	26101100
Voltage Code	S