

PRODUCT-DETAILS

3GAA133340-ARE

(3GAA133340-ARE)



General Information	
Product ID	3GAA133340-ARE
ABB Type Designation	M3AA 132MD 6
Catalog Description	(3GAA133340-ARE)

Ordering	
ABB Type Designation	M3AA 132MD 6
Invoice Description	M3AA 132MD 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA133315-ARE

Electrical							
Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	60 Hz	380 V	7.50 kW	1170 r/min	20.80 A	0.610
D	--	60 Hz	220 V	7.50 kW	1170 r/min	36.00 A	0.610
Temperature Class Default							--
Altitude							1000 m
Ambient Temperature							40 °C
IC Class							IC411
IP Class							IP55
Insulation Class							ICLF
Direction of Rotation							Both sides
Number of Poles (High)							6
Two Speed Motor							No
Type of Duty							S1
Voltage Code							R
Mechanical							
Frame Material							Aluminum
Frame Size							132
IM Class							IMB3 IM1001
Terminator Box Location							D-End top
Dimensions							
Package Level 1 Units							0 carton
Product Net Weight							61 kg
Gross Weight							66 kg
Environmental							
WEEE Category				5. Small Equipment (No External Dimension More Than 50 cm)			
SCIP				27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)			
Classifications							
UNSPSC							26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

