



PRODUCT-DETAILS

3GAA133444-BDE

No Description Available

"No longer for sale" replaced by 3GAA133330-

General Information											
Product ID			3GAA133444-BDE								
ABB Type Designation			M3AA 132MC 6								
Catalog Description			No Description Available								
Additional Information											
ABB Type Designation			M3AA 132MC 6								
Altitude			1000 m								
Ambient Temperature			40 °C								
Bearing			6208-2Z/C3								
Bearing NDE			6208-2Z/C3								
Country of Origin			Spain (ES) Sweden (SE)								
Customs Tariff Number			85015230								
Direction of Rotation			Both sides								
Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	tE
Y	--	50 Hz	660-690 V	5.50 kW	965 r/min	8.00 A	0.680	0.00 %	54.43 N·m	0.00	
D	--	50 Hz	380-420 V	5.50 kW	965 r/min	13.90 A	0.680	0.00 %	54.43 N·m	0.00	0
D	--	60 Hz	440-480 V	6.40 kW	1165 r/min	13.90 A	0.690	0.00 %	52.46 N·m	0.00	0
Frame Material			Aluminum								
Frame Size			132								
Gross Weight			59 kg								
IC Class			IC411								
IM Class			IMB5 IM3001								
Insulation Class			ICLF								
IP Class			IP55								
Lubrication			For life								
Made To Order			No								
Minimum Order Quantity			1 piece								
Number of Poles (High)			6								
Order Multiple			1 piece								
Package Level 1 Units			0 carton								
Product Name			3-Phase squirrel cage motor								

Product Net Weight	59 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA133330-BDE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D