



PRODUCT-DETAILS

3GAA133614-ADJ

No Description Available

"No longer for sale" replaced by 3GAA133330-

General Information

Product ID	3GAA133614-ADJ
ABB Type Designation	M3AA 132MC 6
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 132MC 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Poland (PL) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	400 V	5.50 kW	970 r/min	13.30 A	0.670
Y	--	50 Hz	690 V	5.50 kW	970 r/min	7.00 A	0.680
D	--	50 Hz	415 V	5.50 kW	973 r/min	13.60 A	0.630

Frame Material	Aluminum
Frame Size	132
Gross Weight	65 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 88.5 % Partial Load (75%) 88.8 % Partial Load (50%) 87.3 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	64 kg

Product Type	3AA0_M3AA_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA133330-ADJ
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Temperature Rise	80 K
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D