



PRODUCT-DETAILS

3GAA134003-BSE

No Description Available

"No longer for sale" replaced by 3GAA134360-

General Information											
Product ID	3GAA134003-BSE										
ABB Type Designation	M2AA 132MB 8 HO										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2AA 132MB 8 HO										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6208-2Z/C3										
Bearing NDE	6206-2Z/C3										
Country of Origin	Spain (ES) Sweden (SE)										
Customs Tariff Number	85015220										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	D	--	50 Hz	230 V	3.80 kW	710 r/min	18.10 A	0.680	76.70 %	51.10 N·m	3.70
	Y	--	50 Hz	400 V	3.80 kW	710 r/min	10.50 A	0.680	76.70 %	51.10 N·m	3.70
	Y	--	60 Hz	460 V	3.80 kW	865 r/min	9.10 A	0.650	80.40 %	41.90 N·m	4.20
Frame Material	Aluminum										
Frame Size	132										
Gross Weight	60.38 kg										
IC Class	IC411										
IM Class	IMB5 IM3001										
Insulation Class	ICLF										
IP Class	IP55										
Lubrication	For life										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	8										
Order Multiple	1 piece										
Package Level 1 Units	1 carton										
Product Name	3-Phase squirrel cage motor										
Product Net Weight	59 kg										
Product Type	3AA2 M3AA IE2 AA										

Quote Only	No
Replacement Product ID (NEW)	3GAA134360-BSE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S