



PRODUCT-DETAILS

3GAA134062-ASA

M1AA 132MA 8

"No longer for sale" replaced by 3GAA134300-

General Information	
Product ID	3GAA134062-ASA
ABB Type Designation	M1AA 132MA 8
Catalog Description	M1AA 132MA 8

Additional Information	
ABB Type Designation	M1AA 132MA 8
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Turkiye (TR)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	3.00 kW	710 r/min	14.20 A	0.690
Y	--	50 Hz	400 V	3.00 kW	710 r/min	8.20 A	0.690
Y	--	60 Hz	460 V	3.00 kW	860 r/min	7.50 A	0.640

Frame Material	Aluminum
Frame Size	132
Gross Weight	0 kg
IC Class	IC411
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 78.5 % Partial Load (75%) 75.8 % Partial Load (50%) 74.9 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M1AA 132MA 8
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	8
Order Multiple	1 piece

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	0 kg
Product Type	1AA1__M1AA_IE1_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA134300-ASE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)