



PRODUCT-DETAILS

3GAA134443-BGE

No Description Available

"No longer for sale" replaced by 3GAA134320-

General Information	
Product ID	3GAA134443-BGE
ABB Type Designation	M3AA 132MB 8
EAN	3GAA134443-BGE
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 132MB 8
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Spain (ES) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GAA134443-BGE
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	2.20 kW	730 r/min	6.50 A	0.580

Frame Size	132
Gross Weight	54 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 81.2 % Partial Load (75%) 79.9 % Partial Load (50%) 76.2 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	8
Order Multiple	1 piece

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	54 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA134320-BGE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G