

PRODUCT-DETAILS

3GAA138101-BDB
(3GAA138101-BDB)



General Information	
Product ID	3GAA138101-BDB
ABB Type Designation	M3AA 132S 2/4
Catalog Description	(3GAA138101-BDB)

Ordering	
ABB Type Designation	M3AA 132S 2/4
Invoice Description	M3AA 132S 2/4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220

Electrical	
------------	--

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	2912 r/min	11.20 A	0.820	86.20 %	18.04 N·m	7.60
Y	--	50 Hz	400 V	1.00 kW	1480 r/min	3.98 A	0.540	67.20 %	6.45 N·m	5.70
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 67.2 % Partial Load (75%) 62.5 % Partial Load (50%) 53.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	42 kg
Gross Weight	47 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

