


## PRODUCT-DETAILS

# 3GAA138333-ADB

## (3GAA138333-ADB)

"No longer for sale" replaced by 3GAA138330-



### General Information

Product ID	3GAA138333-ADB
ABB Type Designation	M3AA 132MC 6-12
Catalog Description	(3GAA138333-ADB)

### Ordering

ABB Type Designation	M3AA 132MC 6-12
Invoice Description	M3AA 132MC 6-12
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA138133-ADB

### Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
YY	--	50 Hz	400 V	4.00 kW	950 r/min	9.40 A	0.750	82.00 %	40.20 N·m	6.10
Y	--	50 Hz	400 V	0.75 kW	470 r/min	3.40 A	0.490	65.00 %	15.20 N·m	2.40

Temperature Class Default	--
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class NA Full Load (100%) 65.0 % Partial Load (75%) 60.6 % Partial Load (50%) 45.5 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	Yes
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z-C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	59 kg
Gross Weight	64 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

