

PRODUCT-DETAILS

3GAA169421-ADG (3GAA169421-ADG)



General Information

Product ID	3GAA169421-ADG
ABB Type Designation	M3AA 160MLB 2/4
Catalog Description	(3GAA169421-ADG)

Ordering

ABB Type Designation	M3AA 160MLB 2/4
Invoice Description	M3AA 160MLB 2/4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA168230-ADG

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	15.00 kW	2928 r/min	26.20 A	0.920	89.50 %	49.00 N·m	7.00
Y	--	50 Hz	400 V	7.50 kW	1467 r/min	16.30 A	0.780	84.80 %	49.00 N·m	5.50

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class NA Full Load (100%) 84.8 % Partial Load (75%) 86.8 % Partial Load (50%) 86.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	Yes
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	123 kg
Gross Weight	133 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

