



PRODUCT-DETAILS

3GAA181053-HEK

No Description Available

"No longer for sale" replaced by 3GAA181430-

General Information	
Product ID	3GAA181053-HEK
ABB Type Designation	M3AA 180MLC 2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 180MLC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6310-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE) Poland (PL)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	500 V	37.00 kW	2952 r/min	51.80 A	0.880

Frame Material	Aluminum
Frame Size	180
Gross Weight	194 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 93.7 % Partial Load (75%) 94.5 % Partial Load (50%) 94.5 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)

Pre Modified Motor	3GAA181053-AEK
Product ID	
Product Name	3-Phase squirrel cage motor
Product Net Weight	184 kg
Product Type	3AA3__M3AA_IE3_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA181430-HEK
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)