



PRODUCT-DETAILS

3GAA203051-BEK

No Description Available

"No longer for sale" replaced by 3GAA203410-

General Information

Product ID	3GAA203051-BEK
ABB Type Designation	M3AA 200MLA 6
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 200MLA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	500 V	18.50 kW	990 r/min	29.80 A	0.770
D	--	60 Hz	575 V	18.50 kW	1191 r/min	15.80 A	0.770

Frame Material	Aluminum
Frame Size	200
Gross Weight	228 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 92.9 % Partial Load (75%) 93.2 % Partial Load (50%) 92.7 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 93.3 % Partial Load (75%) 93.2 % Partial Load (50%) 92.1 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)

Product Name	3-Phase squirrel cage motor
Product Net Weight	228 kg
Product Type	3AA3 M3AA IE3 AA
Quote Only	No
Replacement Product ID (NEW)	3GAA203410-BEK
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)