



PRODUCT-DETAILS

3GAA204031-AEG

No Description Available

"No longer for sale" replaced by 3GAA204410-

General Information																															
Product ID	3GAA204031-AEG																														
ABB Type Designation	M3AA 200MLA 8																														
Catalog Description	No Description Available																														
Additional Information																															
ABB Type Designation	M3AA 200MLA 8																														
Altitude	1000 m																														
Ambient Temperature	40 °C																														
Bearing	6312-2Z/C3																														
Bearing NDE	6210-2Z/C3																														
Country of Origin	Sweden (SE)																														
Customs Tariff Number	85015230																														
Direction of Rotation	Both sides																														
Electrical Data																															
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th></tr><tr><td>D</td><td>--</td><td>50 Hz</td><td>500 V</td><td>15.00 kW</td><td>737 r/min</td><td>25.90 A</td><td>0.740</td></tr><tr><td>D</td><td>--</td><td>60 Hz</td><td>575 V</td><td>15.00 kW</td><td>890 r/min</td><td>22.80 A</td><td>0.720</td></tr></table>								Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	D	--	50 Hz	500 V	15.00 kW	737 r/min	25.90 A	0.740	D	--	60 Hz	575 V	15.00 kW	890 r/min	22.80 A	0.720
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor																								
D	--	50 Hz	500 V	15.00 kW	737 r/min	25.90 A	0.740																								
D	--	60 Hz	575 V	15.00 kW	890 r/min	22.80 A	0.720																								
Frame Material	Aluminum																														
Frame Size	200																														
Gross Weight	217 kg																														
IC Class	IC411																														
IM Class	IMB3 IM1001																														
Insulation Class	ICLF																														
IP Class	IP55																														
Made To Order	No																														
Minimum Order Quantity	1 piece																														
Moment of Inertia	0.00000 kg/m³																														
Number of Poles (High)	8																														
Package Level 1 Units	0 pallet (lift)																														
Product Name	3-Phase squirrel cage motor																														
Product Net Weight	217 kg																														
Product Type	3AA2__M3AA_IE2_AA																														
Quote Only	No																														

Replaced Product ID (OLD)	3GAA204001-AEC
Replacement Product ID (NEW)	3GAA204410-AEG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E