



PRODUCT-DETAILS

3GAA208129-ADG

No Description Available

"No longer for sale" replaced by 3GAA209439-

General Information												
Product ID										3GAA208129-ADG		
ABB Type Designation										M3AA 200MLC 4/8		
Catalog Description										No Description Available		
Additional Information												
ABB Type Designation										M3AA 200MLC 4/8		
Altitude										1000 m		
Ambient Temperature										40 °C		
Bearing										6312-Z/C3		
Bearing NDE										6210-ZC3		
Country of Origin										Sweden (SE)		
Customs Tariff Number										85015230		
Direction of Rotation										Both sides		
Electrical Data												
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	tE	IS/IN	
YY	--	50 Hz	400 V	30.00 kW	1481 r/min	54.60 A	0.890	0.00 %	0.00 N·m	0	0.00	
D	--	50 Hz	400 V	17.00 kW	740 r/min	39.40 A	0.710	0.00 %	0.00 N·m	0	0.00	
Frame Material										Aluminum		
Frame Size										200		
Gross Weight										245 kg		
IC Class										IC411		
IM Class										IMB3 IM1001		
Insulation Class										ICLF		
IP Class										IP55		
Made To Order										No		
Minimum Order Quantity										1 piece		
Moment of Inertia										0.00000 kg/m³		
Number of Poles (High)										4		
Number of Poles (Low)										8		
Package Level 1 Units										0 pallet (lift)		
Product Name										3-Phase squirrel cage motor		
Product Net Weight										245 kg		
Product Type										3AA2 M3AA IE2 AA		
Quote Only										No		

Replaced Product ID (OLD)	3GAA208109-ADC
Replacement Product ID (NEW)	3GAA209439-ADG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	Yes
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D