



PRODUCT-DETAILS

3GAA208243-ADG

No Description Available

"No longer for sale" replaced by 3GAA208414-

General Information	
Product ID	3GAA208243-ADG
ABB Type Designation	M3AA 200MLA 4/6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 200MLA 4/6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	tE	IS/IN
Y	--	50 Hz	400 V	23.00 kW	1484 r/min	42.30 A	0.870	0.00 %	0.00 N·m	0	0.00
Y	--	50 Hz	400 V	7.20 kW	989 r/min	14.50 A	0.850	0.00 %	0.00 N·m	0	0.00

Frame Material	Aluminum
Frame Size	200
Gross Weight	230 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	4
Number of Poles (Low)	6
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor

Product Net Weight	218 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA208213-ADC
Replacement Product ID (NEW)	3GAA208414-ADG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	Yes
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D