



PRODUCT-DETAILS

3GAA221034-ADG

No Description Available

"No longer for sale" replaced by 3GAA221240-

General Information	
Product ID	3GAA221034-ADG
ABB Type Designation	M3AA 225SMD 2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 225SMD 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	400 V	80.00 kW	2964 r/min	140.00 A	0.870
Y	--	50 Hz	690 V	80.00 kW	2964 r/min	81.40 A	0.870
D	--	50 Hz	415 V	80.00 kW	2967 r/min	140.00 A	0.840
D	--	60 Hz	460 V	80.00 kW	3570 r/min	120.00 A	0.880

Frame Material	Aluminum
Frame Size	225
Gross Weight	317 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 94.5 % Partial Load (75%) 94.7 % Partial Load (50%) 94.1 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 94.6 % Partial Load (75%) 94.4 % Partial Load (50%) 93.3 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55

Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	2
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	317 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA221240-ADG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D