



PRODUCT-DETAILS

3GAA223054-AEK

No Description Available

"No longer for sale" replaced by 3GAA223220-

General Information								
Product ID	3GAA223054-AEK							
ABB Type Designation	M3AA 225SMB 6							
Catalog Description	No Description Available							
Additional Information								
ABB Type Designation	M3AA 225SMB 6							
Altitude	1000 m							
Ambient Temperature	40 °C							
Bearing	6313-2Z/C3							
Bearing NDE	6212-2Z/C3							
Country of Origin	Sweden (SE) Poland (PL)							
Customs Tariff Number	85015230							
Direction of Rotation	Both sides							
Electrical Data								
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
	D	--	50 Hz	500 V	37.00 kW	985 r/min	57.20 A	0.800
Frame Material	Aluminum							
Frame Size	225							
Gross Weight	317 kg							
IC Class	IC411							
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 93.3 % Partial Load (75%) 94.2 % Partial Load (50%) 94.0 %							
IM Class	IMB3 IM1001							
Insulation Class	ICLF							
IP Class	IP55							
Lubrication	For life							
Made To Order	No							
Minimum Order Quantity	1 piece							
Number of Poles (High)	6							
Order Multiple	1 piece							
Package Level 1 Units	0 pallet (lift)							
Product Name	3-Phase squirrel cage motor							
Product Net Weight	307 kg							
Product Type	3AA3_M3AA_IE3_AA							

Quote Only	No
Replacement Product ID (NEW)	3GAA223220-AEK
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)