



PRODUCT-DETAILS

3GAA228125-ADG

No Description Available

"No longer for sale" replaced by 3GAA229219-

General Information												
Product ID										3GAA228125-ADG		
ABB Type Designation										M3AA 225SMA 4/8		
Catalog Description										No Description Available		
Additional Information												
ABB Type Designation										M3AA 225SMA 4/8		
Altitude										1000 m		
Ambient Temperature										40 °C		
Bearing										6313-2Z/C3		
Bearing NDE										6212-2Z/C3		
Country of Origin										Sweden (SE)		
Customs Tariff Number										85015230		
Direction of Rotation										Both sides		
Electrical Data												
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	tE	IS/IN	
YY	--	50 Hz	400 V	35.00 kW	1479 r/min	62.70 A	0.890	0.00 %	0.00 N·m	0	0.00	
D	--	50 Hz	400 V	21.00 kW	740 r/min	49.50 A	0.690	0.00 %	0.00 N·m	0	0.00	
Frame Material										Aluminum		
Frame Size										225		
Gross Weight										266 kg		
IC Class										IC411		
IM Class										IMB3 IM1001		
Insulation Class										ICLF		
IP Class										IP55		
Made To Order										No		
Minimum Order Quantity										1 piece		
Moment of Inertia										0.00000 kg/m³		
Number of Poles (High)										4		
Number of Poles (Low)										8		
Package Level 1 Units										0 pallet (lift)		
Product Name										3-Phase squirrel cage motor		
Product Net Weight										266 kg		
Product Type										3AA2 M3AA IE2 AA		
Quote Only										No		

Replaced Product ID (OLD)	3GAA228105-ADC
Replacement Product ID (NEW)	3GAA229219-ADG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	Yes
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D