

PRODUCT-DETAILS

3GAA228211-BDG

(3GAA228211-BDG)



General Information

Product ID	3GAA228211-BDG
ABB Type Designation	M3AA 225SMA 2/4
Catalog Description	(3GAA228211-BDG)

Ordering

ABB Type Designation	M3AA 225SMA 2/4
Invoice Description	M3AA 225SMA 2/4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015290

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	43.00 kW	2957 r/min	73.90 A	0.910	92.20 %	139.00 N-m	7.70
Y	--	50 Hz	400 V	6.00 kW	1484 r/min	13.00 A	0.770	86.10 %	39.00 N-m	7.10
Temperature Class Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 86.1 % Partial Load (75%) 86.8 % Partial Load (50%) 85.4 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	286 kg
Gross Weight	296 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

