

PRODUCT-DETAILS

# 3GAA228214-BDG

## (3GAA228214-BDG)



### General Information

Product ID	3GAA228214-BDG
ABB Type Designation	M3AA 225SMA 4/6
Catalog Description	(3GAA228214-BDG)

### Ordering

ABB Type Designation	M3AA 225SMA 4/6
Invoice Description	M3AA 225SMA 4/6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA228242-BDG

Electrical											
Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
D	--	50 Hz	400 V	34.00 kW	1481 r/min	60.60 A	0.890	90.90 %	219.00 N·m	6.70	
Y	--	50 Hz	400 V	11.00 kW	990 r/min	22.30 A	0.830	85.40 %	1067.00 N·m	6.70	
Temperature Class Default											--
Altitude											1000 m
Ambient Temperature											40 °C
IC Class											IC411
IE Class Data (50 Hz)											IE Class NA Full Load (100%) 85.4 % Partial Load (75%) 87.0 % Partial Load (50%) 86.3 %
IP Class											IP55
Insulation Class											ICLF
Direction of Rotation											Both sides
Number of Poles (High)											4
Two Speed Motor											Yes
Type of Duty											S1
Voltage Code											D
Mechanical											
Frame Material											Aluminum
Frame Size											225
Bearing											6313-2Z/C3
Bearing NDE											6212-2Z/C3
IM Class											IMB5 IM3001
Terminator Box Location											D-End top
Dimensions											
Package Level 1 Units											0 pallet (lift)
Product Net Weight											266 kg
Gross Weight											276 kg
Environmental											
WEEE Category											4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP											27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Classifications											
UNSPSC											26101100

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

