



PRODUCT-DETAILS

3GAA228222-BDG
(3GAA228222-BDG)



General Information

Product ID	3GAA228222-BDG
ABB Type Designation	M3AA 225SMB 4/8
Catalog Description	(3GAA228222-BDG)

Ordering

ABB Type Designation	M3AA 225SMB 4/8
Invoice Description	M3AA 225SMB 4/8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015290
Replaced Product ID (OLD)	3GAA228232-BDG

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	400 V	46.00 kW	1483 r/min	88.00 A	0.820	92.00 %	296.00 N·m	7.80
Y	--	50 Hz	400 V	7.00 kW	741 r/min	20.40 A	0.610	81.00 %	90.00 N·m	5.10
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 81.0 % Partial Load (75%) 80.5 % Partial Load (50%) 76.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	Top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	287 kg
Gross Weight	297 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

