

PRODUCT-DETAILS

3GAA229226-ADG
(3GAA229226-ADG)



General Information	
Product ID	3GAA229226-ADG
ABB Type Designation	M3AA 225SMB 6/8
Catalog Description	(3GAA229226-ADG)

Ordering	
ABB Type Designation	M3AA 225SMB 6/8
Invoice Description	M3AA 225SMB 6/8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	400 V	28.00 kW	988 r/min	54.40 A	0.830	89.40 %	271.00 N·m	6.90
D	--	50 Hz	400 V	20.00 kW	741 r/min	45.20 A	0.730	87.30 %	258.00 N·m	6.40
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 87.3 % Partial Load (75%) 88.2 % Partial Load (50%) 87.1 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	300 kg
Gross Weight	310 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

