



PRODUCT-DETAILS

3GAA251061-BSA

No Description Available

"No longer for sale" replaced by 3GAA251210-

General Information	
Product ID	3GAA251061-BSA
ABB Type Designation	M1AA 250SMA 2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M1AA 250SMA 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6315/C3
Bearing NDE	6313-2Z/C3
Country of Origin	Turkiye (TR)
Customs Tariff Number	85015290
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	55.00 kW	2955 r/min	166.00 A	0.900
Y	--	50 Hz	400 V	55.00 kW	2955 r/min	96.20 A	0.900
Y	--	60 Hz	460 V	55.00 kW	3545 r/min	83.20 A	0.900

Frame Material	Aluminum
Frame Size	250
Gross Weight	0 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1
	Full Load (100%) 92.1 %
	Partial Load (75%) 91.8 %
	Partial Load (50%) 90.3 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)

Product Name	3-Phase squirrel cage motor
Product Net Weight	0 kg
Product Type	1AA1__M1AA_IE1_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA251210-BSG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)