



PRODUCT-DETAILS

3GAA252052-HDK

No Description Available

"No longer for sale" replaced by 3GAA252220-

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GAA252052-HDK |
| ABB Type Designation | M3AA 250SMB 4 |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|----------------------------|
| ABB Type Designation | M3AA 250SMB 4 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6315-2Z/C3 |
| Bearing NDE | 6213-2Z/C3 |
| Country of Origin | Sweden (SE) Poland (PL) |
| Customs Tariff Number | 85015290 |
| Direction of Rotation | Both sides |
| Electrical Data | |

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor |
|------|------------|-------|---------|----------|------------|----------|--------------|
| D | -- | 50 Hz | 400 V | 75.00 kW | 1482 r/min | 135.00 A | 0.840 |
| Y | -- | 50 Hz | 690 V | 75.00 kW | 1482 r/min | 78.60 A | 0.840 |
| D | -- | 50 Hz | 415 V | 75.00 kW | 1483 r/min | 133.00 A | 0.820 |

| | |
|------------------------|---|
| Frame Material | Aluminum |
| Frame Size | 250 |
| Gross Weight | 421 kg |
| IC Class | IC411 |
| IE Class Data (50 Hz) | IE Class IE3 Full Load (100%) 95.0 % Partial Load (75%) 95.3 % Partial Load (50%) 94.8 % |
| IM Class | IMB35 IM2001 |
| Insulation Class | ICLF |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 4 |

| | |
|-------------------------------|---|
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 pallet (lift) |
| Pre Modified Motor Product ID | 3GAA252052-ADK |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 411 kg |
| Product Type | 3AA3__M3AA_IE3_AA |
| Quote Only | No |
| Replacement Product ID (NEW) | 3GAA252220-HDK |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | D |
| WEEE Category | 4. Large Equipment (Any External Dimension More Than 50 cm) |