



PRODUCT-DETAILS

3GAL132006-BSB

No Description Available

"No longer for sale" replaced by 3GAL132223-

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GAL132006-BSB |
| ABB Type Designation | M3AL 132SMB 4 |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|---------------|
| ABB Type Designation | M3AL 132SMB 4 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6208-2Z/C3 |
| Bearing NDE | 6208-2Z/C3 |
| Country of Origin | Sweden (SE) |
| Customs Tariff Number | 85015220 |
| Direction of Rotation | Both sides |
| Electrical Data | |

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Efficiency |
|------|------------|-------|---------|---------|------------|---------|------------|
| Y | -- | 50 Hz | 380 V | 7.50 kW | 1500 r/min | 17.40 A | 88.70 % |

| | |
|------------------------|-------------------------------------|
| Frame Material | Aluminum |
| Frame Size | 132 |
| Gross Weight | 48 kg |
| IC Class | IC411 |
| IM Class | IMB5 IM3001 |
| Insulation Class | ICLF |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Moment of Inertia | 0.00000 kg/m³ |
| Number of Poles (High) | 4 |
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 pallet (lift) |
| Product Name | 3Phase Synchronous reluctance motor |
| Product Net Weight | 47 kg |
| Product Type | 3ALO__M3AL_SynRM_AA |

| | |
|------------------------------|---------------------|
| Quote Only | No |
| Replacement Product ID (NEW) | 3GAL132223-BSB |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Frequency Converter |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S9 |
| UNSPSC | 26101100 |
| Voltage Code | S |