



PRODUCT-DETAILS

3GAL132009-BSB

No Description Available

"No longer for sale" replaced by 3GAL132263-

General Information	
Product ID	3GAL132009-BSB
ABB Type Designation	M3AL 132SMF 4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AL 132SMF 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Efficiency
Y	--	50 Hz	380 V	18.50 kW	1500 r/min	42.20 A	91.20 %

Frame Material	Aluminum
Frame Size	132
Gross Weight	90 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)
Product Name	3Phase Synchronous reluctance motor
Product Net Weight	89 kg
Product Type	3ALO__M3AL_SynRM_AA



Quote Only	No
Replacement Product ID (NEW)	3GAL132263-BSB
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Frequency Converter
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S9
UNSPSC	26101100
Voltage Code	S