



PRODUCT-DETAILS

3GBA071211-JSB

No Description Available

General Information											
Product ID	3GBA071211-JSB										
ABB Type Designation	M2BA 71MA 2										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2BA 71MA 2										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6203-2Z/C3										
Bearing NDE	6202-2Z/C3										
Country of Origin	India (IN) China (CN)										
Customs Tariff Number	85015100										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	400 V	0.37 kW	2660 r/min	0.96 A	0.800	69.20 %	1.32 N·m	3.90
	D	--	50 Hz	230 V	0.37 kW	2660 r/min	1.66 A	0.800	69.20 %	1.32 N·m	3.90
	Y	--	60 Hz	460 V	0.37 kW	3325 r/min	0.73 A	0.820	76.70 %	1.06 N·m	5.80
Frame Size	71										
Gross Weight	11.5 kg										
IC Class	IC411										
IM Class	IMB34 IM2101										
Insulation Class	ICLF										
IP Class	IP55										
Lubrication	For life										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	2										
Package Level 1 Units	0 carton										
Product Name	3-Phase squirrel cage motor										
Product Net Weight	11 kg										
Product Type	2BA2_M2BA_IE2_CI										
Quote Only	No										
Selling Unit of Measure	piece										

Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)