



PRODUCT-DETAILS

3GBA073001-BSB

No Description Available

General Information	
Product ID	3GBA073001-BSB
ABB Type Designation	M2BA 71 A6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 71 A6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque
Y	--	50 Hz	380-420 V	0.18 kW	900 r/min	0.62 A	0.720	1.90 N·m
D	--	50 Hz	220-240 V	0.18 kW	900 r/min	1.07 A	0.720	1.90 N·m
Y	--	60 Hz	440-480 V	0.22 kW	1085 r/min	0.65 A	0.740	1.95 N·m

Frame Size	71
Gross Weight	10.26 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg

Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)