



PRODUCT-DETAILS

# 3GBA073211-JFB

## No Description Available

General Information	
Product ID	3GBA073211-JFB
ABB Type Designation	M2BA 71MA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 71MA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	500 V	0.18 kW	900 r/min	0.45 A	0.710	63.70 %	1.91 N·m	3.10
Y	--	60 Hz	575 V	0.18 kW	1120 r/min	0.41 A	0.620	69.00 %	1.53 N·m	4.00

Frame Size	71
Gross Weight	10.5 kg
IC Class	IC411
IM Class	IMB34 IM2101
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg
Product Type	2BA2_M2BA_IE2_CI

Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	F
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)