



PRODUCT-DETAILS

3GBA081310-ASUCN
M2BAK 80MA2

General Information					
Product ID	3GBA081310-ASUCN				
ABB Type Designation	M2BAK 80MA2				
Catalog Description	M2BAK 80MA2				
Additional Information					
ABB Type Designation	M2BAK 80MA2				
Altitude	1000 m				
Ambient Temperature	40 °C				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	Y	--	50 Hz	380 V	0.75 kW
Frame Size					80
Gross Weight					16 kg
IC Class					IC411
IM Class					IMB3 IM1001
Insulation Class					ICLF
Invoice Description					M2BAK 80MA2
IP Class					IP55
Made To Order					No
Minimum Order Quantity					1 piece
Number of Poles (High)					2
Order Multiple					1 piece
Package Level 1 Units					0 carton
Product Name	3-Phase squirrel cage motor				
Product Net Weight					16 kg
Product Type	CBK2__M2BAK_IE2_CI				
Quote Only					No
Selling Unit of Measure					piece
Standards					IEC 60034-1
Starting of Motor					Direct Online

Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)