



PRODUCT-DETAILS

3GBA081320-ASVCN

No Description Available

General Information	
Product ID	3GBA081320-ASVCN
ABB Type Designation	M2BAK80MB2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAK80MB2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	1.10 kW	2910 r/min	4.08 A	0.830	84.30 %	3.61 N·m	30.62
Y	--	50 Hz	380 V	1.10 kW	2910 r/min	2.36 A	0.830	84.30 %	3.61 N·m	17.70

Frame Size	80
Gross Weight	25 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 85.2 % Partial Load (75%) 85.4 % Partial Load (50%) 84.3 %
IE Class Data (60 Hz)	IE Class NA
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S