



PRODUCT-DETAILS

3GBA081340-ASDCNKA
M2BAX 80MD2

General Information	
Product ID	3GBA081340-ASDCNKA
ABB Type Designation	M2BAX 80MD 2
Catalog Description	M2BAX 80MD2

Additional Information	
ABB Type Designation	M2BAX 80MD 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power
Y	--	50 Hz	380 V	1.10 kW

Frame Size	80
Gross Weight	14 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAX 80MD2
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	14 kg
Product Type	CBA3__M2BAX_CI
Quote Only	No

Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)