



PRODUCT-DETAILS

3GBA081443-BHB

No Description Available

General Information	
Product ID	3GBA081443-BHB
ABB Type Designation	M2BA 80MC 2
EAN	3GBA081443-BHB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 80MC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA081443-BHB

Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	1.10 kW	2865 r/min	2.40 A	0.780
Frame Size							80
Gross Weight							19 kg
IC Class							IC411
IE Class Data (50 Hz)							IE Class IE2 Full Load (100%) 80.9 % Partial Load (75%) 80.0 % Partial Load (50%) 77.4 %
IM Class							IMB5 IM3001
Insulation Class							ICLF
IP Class							IP55
Lubrication							For life
Made To Order							No
Minimum Order Quantity							1 piece
Number of Poles (High)							2
Package Level 1 Units							0 carton
Product Name						3-Phase squirrel cage motor	
Product Net Weight							18 kg
Product Type							2BA2__M2BA_IE2_CI

Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)