




PRODUCT-DETAILS

3GBA082420-BSPCN  
(3GBA082420-BSPCN)



General Information

Product ID	3GBA082420-BSPCN
ABB Type Designation	M2BAF 80MLB 4
Catalog Description	(3GBA082420-BSPCN)

Ordering

ABB Type Designation	M2BAF 80MLB 4
Invoice Description	M2BAF 80MLB 4
Product Name	3-Phase squirrel cage motor
Product Type	CBF4__M2BAF_IE4_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380 V	0.75 kW	1455 r/min	1.75 A	0.760	85.70 %	4.93 N·m	7.40
D	--	50 Hz	220 V	0.75 kW	1455 r/min	3.02 A	0.760	85.70 %	4.92 N·m	7.40

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 85.7 % Partial Load (75%) 85.7 % Partial Load (50%) 83.6 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	23 kg
Gross Weight	26 kg

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE4 Super Premium Efficiency Cast Iron Motors

