



PRODUCT-DETAILS

3GBA091212-HFB

No Description Available

General Information																																												
Product ID								3GBA091212-HFB																																				
ABB Type Designation								M2BA 90SLB2																																				
Catalog Description								No Description Available																																				
Additional Information																																												
ABB Type Designation								M2BA 90SLB2																																				
Altitude								1000 m																																				
Ambient Temperature								40 °C																																				
Bearing								6205-2Z/C3																																				
Bearing NDE								6204-2Z/C3																																				
Country of Origin								India (IN) China (CN)																																				
Customs Tariff Number								85015220																																				
Direction of Rotation								Both sides																																				
Electrical Data																																												
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th><th>Torque</th><th>IS/IN</th></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>500 V</td><td>1.50 kW</td><td>2900 r/min</td><td>2.40 A</td><td>0.860</td><td>82.20 %</td><td>4.90 N·m</td><td>7.50</td></tr><tr><td>Y</td><td>--</td><td>60 Hz</td><td>575 V</td><td>1.50 kW</td><td>3505 r/min</td><td>2.00 A</td><td>0.870</td><td>84.40 %</td><td>4.00 N·m</td><td>8.60</td></tr></table>												Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	Y	--	50 Hz	500 V	1.50 kW	2900 r/min	2.40 A	0.860	82.20 %	4.90 N·m	7.50	Y	--	60 Hz	575 V	1.50 kW	3505 r/min	2.00 A	0.870	84.40 %	4.00 N·m	8.60
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN																																		
Y	--	50 Hz	500 V	1.50 kW	2900 r/min	2.40 A	0.860	82.20 %	4.90 N·m	7.50																																		
Y	--	60 Hz	575 V	1.50 kW	3505 r/min	2.00 A	0.870	84.40 %	4.00 N·m	8.60																																		
Frame Size								90																																				
Gross Weight								25 kg																																				
IC Class								IC411																																				
IE Class Data (50 Hz)								IE Class IE2 Full Load (100%) 82.2 % Partial Load (75%) 84.1 % Partial Load (50%) 82.7 %																																				
IE Class Data (60 Hz)								IE Class IE2 Full Load (100%) 84.4 %																																				
IM Class								IMB35 IM2001																																				
Insulation Class								ICLF																																				
IP Class								IP55																																				
Lubrication								For life																																				
Made To Order								No																																				

Minimum Order Quantity	1 piece
Number of Poles (High)	2
Package Level 1 Units	0 carton
Pre Modified Motor Product ID	3GBA091212-AFB
Product Name	3-Phase squirrel cage motor
Product Net Weight	24 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	F
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)