



PRODUCT-DETAILS

3GBA092445-BGB

No Description Available

General Information	
Product ID	3GBA092445-BGB
ABB Type Designation	M2BA 90SLD 4
EAN	3GBA092445-BGB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 90SLD 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA092445-BGB
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	1.50 kW	1440 r/min	3.20 A	0.760

Frame Size	90
Gross Weight	28 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 84.6 % Partial Load (75%) 83.6 % Partial Load (50%) 80.9 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	27 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)